EDITION: JULY 2002 REVISION: JULY 2003 PUBLICATION NO. SM3E-1J50U2

QUICK REFERENCE INDEX

GENERAL INFORMATION MAINTENANCE ENGINE MECHANICAL	MA EM
ENGINE MECHANICAL	EM
ENGINE LUBRICATION & COOLING SYSTEMS	LC
ENGINE CONTROL SYSTEM	EC
ACCELERATOR CONTROL, FUEL & EXHAUST SYSTEMS	FE
AUTOMATIC TRANSMISSION	AT
TRANSFER	TF
PROPELLER SHAFT & DIFFERENTIAL CARRIER	PD
FRONT & REAR AXLE	AX
FRONT & REAR SUSPENSION	SU
BRAKE SYSTEM —————	BR
STEERING SYSTEM	ST
RESTRAINT SYSTEM	RS
BODY & TRIM	BT
HEATER & AIR CONDITIONER	HA
STARTING & CHARGING SYSTEM	SC
ELECTRICAL SYSTEM	EL
ALPHABETICAL INDEX	IDX

INFINITI ® QX4

S

MODEL R50 SERIES



INFINITI®

© 2003 NISSAN MOTOR CO., LTD.

All rights reserved. No part of this Service Manual may be reproduced or stored in a retrieval system, or transmitted in any form, or by any means, electronic, mechanical, photocopying, recording or otherwise, without the prior written permission of Nissan Motor Company Ltd., Tokyo, Japan.

FOREWORD

This manual contains maintenance and repair procedures for the 2003 INFINITI QX4.

In order to assure your safety and the efficient functioning of the vehicle, this manual should be read thoroughly. It is especially important that the PRECAUTIONS in the GI section be completely understood before starting any repair task.

All information in this manual is based on the latest product information at the time of publication. The right is reserved to make changes in specifications and methods at any time without notice.

IMPORTANT SAFETY NOTICE

The proper performance of service is essential for both the safety of the technician and the efficient functioning of the vehicle. The service methods in this Service Manual are described in such a manner that the service may be performed safely and accurately. Service varies with the procedures used, the skills of the technician and the tools and parts available. Accordingly, anyone using service procedures, tools or parts which are not specifically recommended by INFINITI must first be completely satisfied that neither personal safety nor the vehicle's safety will be jeopardized by the service method selected.



NISSAN MOTOR CO., LTD.

Overseas Service Department Tokyo, Japan

INFINITI Your comments are impor Use this form to report an Please print this form and	tant to INFINITI and will help us to y issues or comments you may ha type or write your comments belo Nissan North America, Inc. Technical Service Information 39001 Sunrise Drive, P.O. Box 920 Farmington Hills, MI USA 48331 FAX: (248) 488-3910	ave regarding our Service Manuals. ww. Mail or fax to:
PUBLICATION NO. (Please	photocopy back cover):	
		Production Date:
Please describe any issues of Page number(s)	-	y of each page, marked with your comments.
If no, what page number(s)?_		e? (circle your answer) YES NO ppy of each page, marked with your comments.
-	nanual clear and easy to follow? (c	
What information should b repairing customer vehicle		nuals to better support you in servicing or
		POSITION:
		ADDRESS:
CITY:	STATE/PROV./COUNTRY:	ZIP/POSTAL CODE:

INCH TO METRIC CONVERSION TABLE

(Rounded-off for automotive use)

METRIC TO INCH CONVERSION TABLE (Rounded-off for automotive use)

inches mm inches mm .100 2.54 .610 15.49 .110 2.79 .620 15.75 .120 16.00 3.05 .630 16.26 .130 3.30 .640 .140 3.56 .650 16.51 .150 3.81 16.76 .660 17.02 .160 4.06 .670 .170 4.32 .680 17.27 .180 4.57 .690 17.53 .190 4.83 .700 17.78 .710 18.03 .200 5.08 .210 5.33 .720 18.29 .220 5.59 .730 18.54 .230 5.84 .740 18.80 .240 6.10 .750 19.05 .250 6.35 .760 19.30 .770 .260 6.60 19.56 .270 6.86 .780 19.81 .280 .790 20.07 7.11 .290 7.37 .800 20.32 .300 7.62 .810 20.57 7.87 .820 20.83 .310 .320 8.13 .830 21.08 .330 8.38 .840 21.34 .340 8.64 .850 21.59 .350 8.89 .860 21.84 9.14 .870 22.10 .360 .370 9.40 .880 22.35 .890 22.61 .380 9.65 .390 9.91 .900 22.86 .400 10.16 .910 23.11 .410 10.41 .920 23.37 .420 10.67 .930 23.62 .430 10.92 .940 23.88 .440 .950 11.18 24.13 24.38 .450 11.43 .960 11.68 .970 24.64 .460 11.94 .470 .980 24.89 .480 12.19 .990 25.15 .490 12.45 1.000 25.40 .500 12.70 2.000 50.80 .510 12.95 3.000 76.20 13.21 .520 4.000 101.60 .530 13.46 5.000 127.00 .540 13.72 6.000 152.40 .550 13.97 7.000 177.80 .560 14.22 8.000 203.20 .570 14.48 9.000 228.60 .580 14.73 10.000 254.00 14.99 508.00 .590 20.000 15.24 .600

mm inches mm inches 1 .0394 51 2.008 2 .079 52 2.047 3 .118 53 2.087 4 .157 54 2.126 5 .197 55 2.165 6 .236 56 2.205 7 .276 57 2.244 8 .315 58 2.283 9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.559 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69	
2 .079 52 2.047 3 .118 53 2.087 4 .157 54 2.126 5 .197 55 2.165 6 .236 56 2.205 7 .276 57 2.244 8 .315 58 2.283 9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.599 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71	
3 .118 53 2.087 4 .157 54 2.126 5 .197 55 2.165 6 .236 56 2.205 7 .276 57 2.244 8 .315 58 2.283 9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.598 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72	
4 .157 54 2.126 5 .197 55 2.165 6 .236 56 2.205 7 .276 57 2.244 8 .315 58 2.283 9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.598 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73	
5 .197 55 2.165 6 .236 56 2.205 7 .276 57 2.244 8 .315 58 2.283 9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.559 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74	
6 .236 56 2.205 7 .276 57 2.244 8 .315 58 2.283 9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.599 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75	- - - - - - - - - - - - - - - - - - -
7 .276 57 2.244 8 .315 58 2.283 9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.599 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76	- - - - - - - - - - - - - - - - - - -
8 .315 58 2.283 9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.598 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 <th>)</th>)
8 .315 58 2.283 9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.598 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 <th>)</th>)
9 .354 59 2.323 10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.599 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78<	
10 .394 60 2.362 11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.559 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 7)))
11 .433 61 2.402 12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.598 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181)))
12 .472 62 2.441 13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.559 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 <td< th=""><th>)</th></td<>)
13 .512 63 2.480 14 .551 64 2.520 15 .591 65 2.559 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 <t< th=""><th>)</th></t<>)
14 .551 64 2.520 15 .591 65 2.559 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 <)
15 .591 65 2.559 16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268)
16 .630 66 2.598 17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
17 .669 67 2.638 18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
18 .709 68 2.677 19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
19 .748 69 2.717 20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
20 .787 70 2.756 21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
21 .827 71 2.795 22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
22 .866 72 2.835 23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
23 .906 73 2.874 24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
24 .945 74 2.913 25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
25 .984 75 2.953 26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
26 1.024 76 2.992 27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
27 1.063 77 3.031 28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
28 1.102 78 3.071 29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
29 1.142 79 3.110 30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
30 1.181 80 3.150 31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
31 1.220 81 3.189 32 1.260 82 3.228 33 1.299 83 3.268	
32 1.260 82 3.228 33 1.299 83 3.268)
33 1.299 83 3.268	
	,
34 1.339 84 3.307	,
35 1.378 85 3.346	
36 1.417 86 3.386	
37 1.457 87 3.425	
38 1.496 88 3.465	
39 1.535 89 3.504	
40 1.575 90 3.543	
41 1.614 91 3.583	
42 1.654 92 3.622	
43 1.693 93 3.661	
44 1.732 94 3.701	
45 1.772 95 3.740	
45 1.772 95 3.740 46 1.811 96 3.780	
48 1.890 98 3.858	
49 1.929 99 3.898	
50 1.969 100 3.937	1

TEST VALUE AND TEST LIMIT (GST ONLY - NOT APPLICABLE TO CONSULT-II)

The following is the information specified in Mode 6 of SAE J1979.

The test value is a parameter used to determine whether a system/circuit diagnostic test is "OK" or "NG" while being monitored by the ECM during self-diagnosis. The test limit is a reference value which is specified as the maximum or minimum value and is compared with the test value being monitored.

These data (test value and test limit) are specified by Test ID (TID) and Component ID (CID) and can be displayed on the GST screen.

SRT item	Self-diagnostic test item	DTC	Test value (GST display)		Test limit	Conversion
			TID	CID		
CATALYST -	Three way catalyst function (Bank 1)	P0420	01H	01H	Max.	1/128
		P0420	02H	81H	Min.	1
	Three way catalyst function (Bank 2)	P0430	03H	02H	Max.	1/128
		P0430	04H	82H	Min.	1
	EVAP control system (Small leak)	P0442	05H	03H	Max.	1/128mm ²
	EVAP control system purge flow monitoring	P0441	06H	83H	Min.	20mV
EVAP SYSTEM	EVAP control system (Very small leak)	P0456	07H	03H	Max.	1/128mm ²
		P1456	07H	03H	Max.	1/128mm ²
		P0133	09H	04H	Max.	16ms
		P1143	0AH	84H	Min.	10mV
	Heated oxygen sensor 1 (Bank 1)	P1144	0BH	04H	Max.	10mV
		P0132	0CH	04H	Max.	10mV
		P0134	0DH	04H	Max.	1s
	Heated oxygen sensor 1 (Bank 2)	P0153	11H	05H	Max.	16ms
		P1163	12H	85H	Min.	10mV
		P1164	13H	05H	Max.	10mV
		P0152	14H	05H	Max.	10mV
HO2S		P0154	15H	05H	Max.	1s
	Heated oxygen sensor 2 (Bank 1)	P0139	19H	86H	Min.	10mV/500ms
_		P1147	1AH	86H	Min.	10mV
		P1146	1BH	06H	Max.	10mV
		P0138	1CH	06H	Max.	10mV
	Heated oxygen sensor 2 (Bank 2)	P0159	21H	87H	Min.	10mV/500ms
		P1167	22H	87H	Min.	10mV
		P1166	23H	07H	Max.	10mV
		P0158	24H	07H	Max.	10mV
	Heated oxygen sensor 1 heater (Bank 1)	P0032	29H	08H	Max.	20mV
		P0031	2AH	88H	Min.	20mV
F	Heated oxygen sensor 1 heater (Bank 2)	P0052	2BH	09H	Max.	20mV
		P0051	2CH	89H	Min.	20mV
HO2S HTR	Heated oxygen sensor 2 heater (Bank 1)	P0038	2DH	0AH	Max.	20mV
		P0037	2EH	8AH	Min.	20mV
F	Heated oxygen sensor 2 heater (Bank 2)	P0058	2FH	0BH	Max.	20mV
		P0057	30H	8BH	Min.	20mV